











NOTES:
1.CAGE: COPPER ALLOY THICKNESS:0.25mm;
2.CLIP: STAINLESS STEEL
3.LIGHT PIPE: POLYCARBONATE COLOR CLEAR









RECOMMENDED PCB LAYOUT (COMPONENT SIDE)

RECOMMENDED MINIMUM PCB THICKNESS:1.50mm
(ALL TOLERANCES ARE ±0.05)

RECOMMENDED PCB CONFIGURATION WITH KEEP-OUT
AREAS SINGLE SIDED APPLICATIONS





RECOMMENDED PCB LAYOUT (COMPONENT SIDE)

RECOMMENDED MINIMUM PCB THICKNESS:2.25mm
(ALL TOLERANCES ARE ±0.05)

RECOMMENDED PCB CONFIGURATION WITH
KEEP-OUT AREAS BELLY TO BELLY APPLICATIONS

深圳市华灿天禄电子有限公司
工程专用章

1	初版发行	
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE

GENERL TOLERANCE		
DIM	TOL	
X.X	±0.30	
X.XX	±0.20	
X.XXX	±0.10	
Angle	±3.0°	

制 图 DRAWING	
审 核 CHECK	
批 准 APPROVAL	
比 例 SCALE	
投 影 Projection	

深圳市华灿天禄电子有限公司
ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	SPF 外壳（压接式 带导光柱）	版 本 REV.	A
产品料号 PART NO.	HC-SFP-1x4-05L-WLP-03	单 位 UNITS	mm
材 料 MATERIAL		页 次 SHEET	1/1