

# USB 3.0 SuperSpeed Device Cable (A to Micro-B M/M) Black, 6 ft. (1.83 m)

## MODEL NUMBER: U326-006-BK





### **Highlights**

- 6-ft. SuperSpeed USB 3.0 A to Micro B Cable
- 10 times faster than USB 2.0, with transfer rates up to 5 Gbps

### **System Requirements**

 Computers and Peripherals with USB 3.0 capabilities

#### Package Includes

 6-ft. SuperSpeed USB 3.0 A Male to Micro B Male Device Cable - Black

Connects a USB3.0 enabled computer to a USB3.0 peripheral with Micro B type connector

#### **Features**

- 6-ft. SuperSpeed USB 3.0 A Male to Micro B Male Black
- SuperSpeed USB is 10 times faster than Hi-Speed USB, with transfer rates up to 5 Gbps.
- Sync-N-Go technology minimizes user wait-time.
- Provides Optimized Power Efficiency...No device polling and lower active and idle power requirements.
- Backwards compatible with USB 2.0. Devices interoperate with USB 2.0 platforms. Hosts support USB 2.0 legacy devices.

# **Specifications**

OVERVIEW		
UPC Code	037332183163	
Technology	USB 3.x	
Cable Type	Passive	
PHYSICAL		
Material of Construction	PVC	
Cable Jacket Color	Black	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5MM	
Cable Length (ft.)	6	
Cable Length (m)	1.83	



Cable Length (in.)	72	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.18	
Shipping Weight (kg)	0.08	
ENVIRONMENTAL		
Operating Temperature Range	14° to 140°F (-10° to 60°C)	
Storage Temperature Range	-4° to 185°F (-20° to 85°C)	
Relative Humidity	10% to 85%, Non-Condensing	
CONNECTIONS		
Side A - Connector 1	USB 3.0 A (MALE)	
Side B - Connector 1	USB 3.0 MICRO-B (MALE)	
Connector Plating	Nickel	
Contact Plating	Gold	
Connector Style	Straight	
FEATURES & SPECIFICATIONS		
USB Specification	USB 3.0 (up to 5 Gbps)	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.