

Specification Sheet

Part Number: T150XL0HSX2



Heat stabilized heavy duty cable ties provide excellent resistance to high heat exposures.
Head design provides high tensile strength with very low insertion force.

Heavy Duty Cable Tie, 43" Long, UL Rated, 175lb Tensile Strength, PA66HS, Black, 25/pkg

Article Number	111-15510
Type	T150XL
Color	Black (BK)
Quantity Per	bag
Product Description	Heavy duty T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. Durable head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
Short Description	Heavy Duty Cable Tie, 43" Long, UL Rated, 175lb Tensile Strength, PA66HS, Black, 25/pkg
Global Part Name	T150XL-PA66HS-BK

Minimum Tensile Strength (Imperial)	175.0
Minimum Tensile Strength (Metric)	780.0
Length L (Imperial)	43.0
Length L (Metric)	1095.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.35
Width W (Metric)	8.9
Bundle Diameter Min (Imperial)	6.0
Bundle Diameter Min (Metric)	152.0
Bundle Diameter Max (Imperial)	13.0
Bundle Diameter Max (Metric)	330.0
Thickness T (Imperial)	0.083
Thickness T (Metric)	2.1

Material	Polyamide 6.6 heat stabilized (PA66HS)
Material Shortcut	PA66HS
Flammability	UL 94 V-2
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +257°F (-40°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL ANSI/UL 746B UL ANSI/UL 1565 UL ANSI/UL 62275
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)