

Specification Sheet

Part Number: 156-01093



The 360 degree enclosure ensures the entire bundle is secure when being routed by this clip.

Locking tab on this clip is small enough that it will not interfere with any other portion of the wire routing, but is significant enough to allow for manual disengagement if service is needed.

The cable tie portion of this two-piece design allows for 2 wire bundles to be routed with the same piece.

Locking Clip, 10-14mm, Assembled with T50R, PA66HIRHS, Black, 2000/CTN

Article Number	156-01093
----------------	-----------

Type	T50RLOC10-14
------	--------------

Color	Black (BK)
-------	------------

Quantity Per	box
--------------	-----

Product Description	HellermannTyton's Two-piece cable tie assembly offers dual bundle routing. The clip portion creates a full and secure lock completely around one bundle, while the cable tie creates a secure solution for a second bundle.
---------------------	---

Short Description	Locking Clip, 10-14mm, Assembled with T50R, PA66HIRHS, Black, 2000/CTN
-------------------	--

Global Part Name	T50RLOC10-14-PA66HS/PA66HIRHS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	220.0
Length L (Imperial)	1.72
Length L (Metric)	43.73
Fixation Method	Omega Clips
Identification Plate Position	none
Width W (Imperial)	0.47
Width W (Metric)	12.0
Bundle Diameter Min (Imperial)	0.39
Bundle Diameter Min (Metric)	10.0
Bundle Diameter Max (Imperial)	0.55
Bundle Diameter Max (Metric)	14.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut	PA66HIRHS PA66HS
UV Resistant (Yes/No)	No
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)