

Specification Sheet

Part Number: 151-15500



Adjustable-height feature allows the clamp to close to the exact height of the ribbon cable

Releasable for easy access to cables when necessary

Available in adhesive or screw-mount versions

Flat Ribbon Cable Clamp, Adhesive, 2.22" Hole Dia, PA66HIR, Black, 100/pkg

Article Number	151-15500
----------------	-----------

Type	FKH50A
------	--------

Color	Black (BK)
-------	------------

Quantity Per	pcs.
--------------	------

Product Description	HellermannTyton's flat ribbon clamps route, protect and secure flat ribbon cables without damage to sensitive wires and cables. The unique, adjustable height feature allows the clamp to close to the exact height of the ribbon cable, using only as much force as needed to secure the cable. The releasable feature allows simple opening when access to the cable is necessary. These clamps are available in adhesive or screw mount versions.
---------------------	--

Short Description	Flat Ribbon Cable Clamp, Adhesive, 2.22" Hole Dia, PA66HIR, Black, 100/pkg
-------------------	--

Global Part Name	FKH50A-PA66HIR-BK
Length L (Imperial)	2.22
Length L (Metric)	56.5
Fixation Method	Pasting / Stick
Variant	Mounting clip
Width W (Imperial)	0.98
Width W (Metric)	25.0
Mounting Hole Diameter D (Imperial)	0.122
Mounting Hole Diameter D (Metric)	3.1 mm
Mounting Hole Diameter D Min (Imperial)	0.122
Mounting Hole Diameter D Max (Imperial)	0.122
Mounting Hole Diameter D Max (Metric)	3.1
Material	Polyamide 6.6, high impact modified (PA66HIR)
Material Shortcut	PA66HIR
Adhesive	Acrylate with base of polyurethane foam

Flammability	UL 94 HB (excluding adhesive)
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	to +221°F (+105°C)
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).