

SAC-3P-22AWG-OE-OE-535-100,0SH - Cable reel



1422032

<https://www.phoenixcontact.com/us/products/1422032>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, shielded, PVC, black, 3-wire, color single wire: brown, blue, black, cable length: 100 m

Commercial data

Item number	1422032
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BF16
Product key	BF1IIB
GTIN	4055626324975
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Customs tariff number	85444290
Country of origin	US

SAC-3P-22AWG-OE-OE-535-100,0SH - Cable reel



1422032

<https://www.phoenixcontact.com/us/products/1422032>

Technical data


Product properties

Product type	Cable by the meter
Number of positions	3
Application	Connector

Cable/line

Cable length	100 m
--------------	-------

Black PVC 105°C [535]

Dimensional drawing	
Cable weight	40 kg/km
UL AWM Style	2517 (105 °C / 300 V)
Number of positions	3
Shielded	yes
Cable type	Black PVC 105°C [535]
Conductor structure signal line	30x 1.30 mm
AWG signal line	22
Wire diameter incl. insulation	1.27 mm ±0.03 mm
External cable diameter	5.2 mm ±0.2 mm
Outer sheath, material	PVC
External sheath, color	black
Conductor material	Tin-plated Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, black
Overall twist	3 wires, twisted
Optical shield covering	85 %
Nominal voltage, cable	300 V
Minimum bending radius, flexible installation	12 x D
Flame resistance	FT4
Other resistance	UV resistant
Special properties	UL standards PLTC and ITC
Ambient temperature (operation)	-30 °C ... 105 °C (cable, fixed installation) -5 °C ... 105 °C (Cable, flexible installation)

SAC-3P-22AWG-OE-OE-535-100,0SH - Cable reel



1422032

<https://www.phoenixcontact.com/us/products/1422032>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1422032>



EAC

Approval ID: RU C-DE.BL08.B.00286



UL Listed

Approval ID: FILE E 344675



cUL Listed

Approval ID: FILE E 344675

cULus Listed

SAC-3P-22AWG-OE-OE-535-100,0SH - Cable reel



1422032

<https://www.phoenixcontact.com/us/products/1422032>

Classifications

ECLASS

ECLASS-11.0	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801

ETIM

ETIM 7.0	EC003249
----------	----------



1422032

<https://www.phoenixcontact.com/us/products/1422032>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com