

Specification Sheet

Part Number: 170-03232



Self-wrapping feature allows easy installation and future access to wire and cables.

Unique blend and construction using monofilament and multifilament strands provide flexibility, high coverage and abrasion resistance.

Extra overlapping design keeps wires contained even in tight bend conditions.

Braided Sleeving, Woven Convoluted Wrap, 5/16" Dia, PET, Orange, 325 ft/reel

Article Number	170-03232
Type	BSPW516
Color	Orange (OG)
Quantity Per	reel
Product Description	This split, wrap-around style woven convoluted sleeving utilizes a unique elastic construction for added flexibility and abrasion resistance. The overlapping design creates material memory allowing the sleeve to quickly roll back over connectors and splices without exposing bundled cabling.
Short Description	Braided Sleeving, Woven Convoluted Wrap, 5/16" Dia, PET, Orange, 325 ft/reel

Global Part Name	BSPW516-PET-OG
------------------	----------------

Length L (Imperial)	325.0
---------------------	-------

Length L (Metric)	99.1
-------------------	------

Bundle Diameter Min (Imperial)	0.098
--------------------------------	-------

Bundle Diameter Min (Metric)	2.5
------------------------------	-----

Bundle Diameter Max (Imperial)	0.31
--------------------------------	------

Bundle Diameter Max (Metric)	8.0
------------------------------	-----

Diameter D (Imperial)	0.313
-----------------------	-------

Diameter D (Metric)	8.0
---------------------	-----

Nominal Diameter (Imperial)	0.315
-----------------------------	-------

Nominal Diameter (Metric)	8.0
---------------------------	-----

Wall Thickness WT (Imperial)	0.027
------------------------------	-------

Wall Thickness WT (Metric)	0.7
----------------------------	-----

Material	Polyester (PET)
----------	-----------------

Material Shortcut	PET
-------------------	-----

Flammability	FMVSS 302 UL 94 V-0
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-94°F to +302°F (-70°C to +150°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	325.0
Package Quantity (Metric)	99.1
Customs Number	5806322000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).