

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: SJT 16/2,105C,BLACK BULK CABLE	
	Model No. <a href="#">Power Cord</a>	
	Part No./Ordering No. <a href="#">H-137</a>	Rev B1

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

- ISO13485:2003 - Medical Devices Quality Management System Certification
- ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <http://www.globtek.com/iso-certificates/>

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek TERMS AND CONDITIONS (attached to the end of this document), which supersede all other agreements, terms, and conditions (<http://en.globtek.com/terms-and-conditions/>).

Prop 65 Statement:<https://en.globtek.com/prop-65-statement.pdf>

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek products are intended for use with commercial, medical, and/or industrial equipment only. GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.

Contents of this document are subject to change without prior notice.

**Customer Approval of Specification:**

Please approve, sign and send back to GlobTek so we can complete order processing.

A delay in receipt of this form will delay delivery schedule.

Company Name:	Customer P/N:
Quote Number:	Date:
Authorized Representative Name:	Authorized Representative Signature:


GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: SJT 16/2,105C,BLACK BULK CABLE	
	Model No. <a href="#">Power Cord</a>	Part No./Ordering No. <a href="#">H-137</a>
		Rev B1

## REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
B1	Change packing to 500 meter on a roll with UOM: 1m	dhock	05/26/2023	QA
B	Update Unit of measure: 1.0m, packed on a roll to 500 feet, packed on a roll	QA	04/19/2023	QA
A	Initial release	QA	11/21/2022	QA

AGENCY ONLINE DOCUMENTS	<a href="http://en.globtek.com/cordsets/">http://en.globtek.com/cordsets/</a>
RoHS/RoHS3 Declaration	<a href="https://www.globtek.com/pdf/rohs_cert/01t3000002p8yGAAQ">https://www.globtek.com/pdf/rohs_cert/01t3000002p8yGAAQ</a>
REACH Declaration	<a href="https://www.globtek.com/pdf/iso_certificates/REACH.pdf">https://www.globtek.com/pdf/iso_certificates/REACH.pdf</a>
Conflict Minerals Declaration	<a href="https://www.globtek.com/pdf/conflict-minerals.pdf">https://www.globtek.com/pdf/conflict-minerals.pdf</a>
Prop 65 Statement	<a href="https://en.globtek.com/prop-65-statement.pdf">https://en.globtek.com/prop-65-statement.pdf</a>

IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.  
 2 conductor round wire



Conductor construction: 26/0.254±0.008  
 Insulation outer diameter: Ø3.05±0.1  
 Insulation Thickness: Minimum 0.69 mm:  
 Coated outer diameter: Ø7.8 ± 0.2  
 Coating Thickness: Minimum 0.61mm  
 Conductor: Bare Copper;  
 Cover: PVC SJT 16AWG\*2C 105°C, core wire color: black, white, sheath: black, ringarranty material  
 Printed on the wire is: (UL) Exxxxxx SJT 105°C 2X16AWG (1.31mm<sup>2</sup>) 300V VW-1 yyyyyyy CSA zzzzzzz TYPE  
 SJT 105°C 2X1.31mm<sup>2</sup>(16AWG) 300V VW-1  
 xxxxxx = UL File #, YYYYYYY MFG Name GlobTek or other, zzzzzzz = CSA or cUL file number  
 Color: Black

### Packing:

500 meters on a roll

UOM = 1m

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: SJT 16/2,105C,BLACK BULK CABLE	
	Model No. <a href="#">Power Cord</a>	
	Part No./Ordering No. <a href="#">H-137</a>	Rev B1

**PACKAGING**

Packing Spec P/N:

Box Qty: 1

Gift Box Size (mm):

Gift Box Color: White

Master Carton Size (mm): TBD

Master Carton Cubic Volume (m³): 0.00

Master GW (Kg): kg

wt Ea. (Kg): kg

wt Ea. (Kg): kg

LABEL SPECS: ,

PACK SPEC: