



2 Pin



3D 图示（参考）

Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:3A AC/DC
额定电流：3A AC/DC
Withstanding voltage:800V AC/minute
耐受电压：800V AC/分钟
Temperature range:-40℃-+85℃
温度范围：-40℃-+85℃
Insulation resistance:1000MΩ min
绝缘电阻：1000MΩ Min
Contact resistance:20mΩ Max
接触电阻：20mΩ Max







A-A

X2011 H F - 08 A - N0
① ② ③ ④ ⑤ ⑥

1.Series No
2.Category:H-HSG
3.Category:F-Female Housing
4.Row No.Pin No:XX-02~15 Pin
5.Special No:A-With Lock
6.Material:N0-PA66 UL94V-0

Circuit 1



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	5.98	09	16.00	19.98
03	4.00	7.98	10	18.00	21.98
04	6.00	9.98	11	20.00	23.98
05	8.00	11.98	12	22.00	25.98
06	10.00	13.98	13	24.00	27.98
07	12.00	15.98	14	26.00	29.98
08	14.00	17.98	15	28.00	31.98

X2011HF-08A-N0	PA66	X2011W	X2011TM
PART N0	Material	Suitable XKB Wafer	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2011HF-08A-N0
CHKD		UNIT: mm/in	DWG NO.: X-X2011HF-08A-N0
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0