

Specification Sheet

Part Number: TAG38T4-100B



HellermannTyton Self-Laminating Labels come on rolls on a standard 3" core for easy loading into a printer or caddy. Labels are conformable so that they can bend around small gauge wires and tight bends without coming loose over time. Labels are UL recognized for indoor and outdoor use to expand application options.

HellermannTyton thermal transfer labels work in any thermal transfer printer so that the use always has options to get labels printed without being locked into a single vendor.

Article Number	596-00011
Type	TAG38T4
Color	White (WH)
Quantity Per	roll
Product Description	HellermannTyton thermal transfer self-laminating labels are a conformable vinyl film with a white printable surface followed by a clear tail that laminates the printed text when applied to a wire or cable. The labels are UL recognized for indoor and outdoor use with an aggressive acrylic adhesive that allows the label to bond to large and small diameter wires.

Short Description	Thermal Transfer Labels, Self-Laminating, 1.0" x 1.5" x 7.37", 4 Across, VL, White, 1000/roll
Global Part Name	TAG38T4-100B-WH
Width W (Imperial)	1.0
Width W (Metric)	25.4
Bundle Diameter Min (Imperial)	0.81
Bundle Diameter Min (Metric)	20.8
Bundle Diameter Max (Imperial)	1.87
Bundle Diameter Max (Metric)	47.5
Thickness T (Metric)	25
Width of Liner (Metric)	104.14
Width of Liner (Imperial)	4.10
Material	Type 100B (100B)
Material Shortcut	100B
Adhesive	Acrylic

Halogen Free	No
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-51°F to +200°F (-46°C to +93°C)
Operating Temperature	-40°F to +205°C (-40 °C to +96 °C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3919102055
Labels per Column	1
Labels per Row	4

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.
(www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)