

Specification Sheet

Part Number: 132-00008



Unique two piece tie allows parallel entry and exit through the head for easy assembly.

High impact, heat stabilized material gives strength needed for trucking and heavy equipment applications.

Button Head Cable Tie with Retainers and Pilot Bushings, 10.5" Long, PA66HIRHSUV, Black, 50/pkg

Article Number	132-00008
----------------	-----------

Type	BT130RDP
------	----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The button head tie is a two piece tie providing for parallel entry and exit through the head. The strap contains serrations on both sides, and has two opposed pawls recessed within a domed head. This design allows the strap to be directed clockwise or counter-clockwise prior to insertion into the head, enabling bi-directional looping.
---------------------	---

Short Description	Button Head Cable Tie with Retainers and Pilot Bushings, 10.5" Long, PA66HIRHSUV, Black, 50/pkg
-------------------	---

Global Part Name	BT130RDP-PA66HIRHSUV-BK
------------------	-------------------------

Minimum Tensile Strength (Imperial)	130.0
Minimum Tensile Strength (Metric)	578.0
Length L (Imperial)	10.5
Length L (Metric)	267.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.3
Width W (Metric)	7.6
Bundle Diameter Min (Imperial)	0.25
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	2.9
Bundle Diameter Max (Metric)	73.0
Mounting Hole Diameter D (Metric)	25.4 mm

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Material Head	Polyamide 6.6 heat stabilized (PA66HS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).