

Specification Sheet

Part Number: 151-00992



Clip can be installed by hand – no need for hardware or tools.
Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Article Number	151-00992
Type	SOC11FTOVAL
Color	Black (BK)
Quantity Per	carton
Product Description	Standoff bundling clips provide a straightforward way to secure cable bundles, hoses or pipes. The bundle fastens to the tape bar using tape or cable ties. Multiple orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standoff keeps bundles away from mounting area to prevent them from damage due to rubbing.
Short Description	Standoff Bundling Clip, 1.97" Long, Panel Thickness 0.02–0.27", PA66HIRHSUV, Black, 3000/carton

Global Part Name	SOC11FTOVAL-PA66HIRHSUV-BK
Length L (Imperial)	1.97
Length L (Metric)	50.0
Offset Length (Imperial)	0.79
Offset Length (Metric)	20.0
Fixation Method	Fir Tree for oval holes
Height H (Imperial)	0.79
Height H (Metric)	20.1
Panel Thickness Min (Imperial)	0.023
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 " 0.26 x 0.50 " 0.26 x 0.51 " 0.28 x 0.47
Mounting Hole Diameter D (Metric)	6.2 x 12.2 mm 7.0 x 12.0 mm 6.5 x 13.0 mm 6.5 x 12.5 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51

Mounting Hole Diameter D Max (Metric)	13.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.

