

Safe-IT USB-A to Lightning Sync/Charge Antibacterial Cable (M/M), Ultra Flexible, MFi Certified, Light Blue, 6 ft. (1.83 m)

MODEL NUMBER: M100AB-006-S-LB



USB/Lightning cable with antibacterial material connects your Apple iPhone, iPad or iPod to the USB-A port on your computer or wall/car charger.

Features

USB Cable Charges and Syncs Your Latest-Generation iPhone, iPad and iPod

This Safe-IT™ sync/charge cable (M/M) connects your iPhone, iPad or iPod to the USB-A port on a computer, laptop, car charger or wall charger. It allows you to charge and power your Apple device, while simultaneously syncing and transferring photos, MP3s and other important files at USB 2.0 data transfer speeds up to 480 Mbps. The cable is backward compatible with previous USB generations, allowing you to use it with older equipment.

Innovative Soft Cable Jacket Prevents Tangles, Allows Flexible Bends

Very flexible for convenient on-the-go connections, this ultra-soft silicone-layered jacket avoids nasty tangles in your backpack or laptop bag and feels nice to the touch. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

Provides Extra Protection Against Certain Bacteria

The molded connectors and jacket are constructed using an antibacterial material that is effective in inhibiting Escherichia coli (E. coli) and Staphylococcus aureus (staph). This added protection makes this Safe-It cable an ideal solution for medical facilities, schools, businesses, restaurants/kitchens and anywhere else that needs extra protection against bacteria.

MFi-Certified for Broad Device Compatibility

The 5V 2.4A (12W max) Lightning cable is MFi-certified for use with the latest generation of compatible iPhone, iPad and iPod devices. Integral strain relief gives the cable extra flexibility, reduces stress and helps the cable move freely without cracking or breaking loose from the connector.

Light Blue Jacket Helps Avoid Misidentification That Can Cause Costly Downtime

The USB cable has a light blue jacket, which is easy to identify quickly in a crowded charging station and helps prevent the cable from becoming accidentally disconnected.

Specifications

Highlights

- Soft, flexible silicone jacket allows easy bending and avoids messy tangling
- MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod
- Constructed with antibacterial material proven effective in inhibiting E. coli and staph
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charges and data transfers
- Light blue jacket permits fast, easy identification in a crowded charging station

Applications

- Charge and sync your Apple iPhone, iPad or iPod using the USB port on your computer or a wall charger up to 6 feet away
- Transfer photos and other important files between an external hard drive and your Apple device
- Provide extra protection against bacteria to give cable installers and IT personnel peace of mind during installation

System Requirements

- Computer, laptop or charger with USB-A port
- Most current iPhone, iPad and iPod devices with Lightning connectors

Package Includes

M100AB-006-S-LB USB-A to Lightning Sync/Charge Antibacterial Cable (M/M), Light Blue, 6 ft. (1.8 m)

OVERVIEW	
UPC Code	037332278265
Technology	Lightning; USB 2.0 (High Speed)
Cable Type	Passive
PHYSICAL	
Material of Construction	JACKET: SILICONE; CONNECTOR: TPE
Cable Jacket Color	Light Blue
Cable Jacket Material	Silicone
Cable Jacket Rating	FT2
Cable Outer Diameter (OD)	4.4mm
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	0.91 x 4.57 x 2.36
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non-Condensing
Power Provided to Connected Device(s)	12W (5V/2.4A)
CONNECTIONS	
Side A - Connector 1	USB A (MALE)
Side B - Connector 1	LIGHTNING (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
Antibacterial	Yes

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

STANDARDS & COMPLIANCE	
Product Certifications	MFi; UL 94
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.