



Main

| | |
|----------------------|------------------|
| Product range | Thorsman Cintura |
| Product type | Cradle base |
| Colour | Clear |
| Quantity per package | 100 pieces |

Complementary

| | |
|---------------------|------------------------------|
| Product destination | For 7.8 mm tie width maximum |
| Condition of use | Indoor |
| Fixing Mode | By rivet By screw |
| Material | PA (polyamide) 6.6 |
| Height | 0.87 in (22.2 mm) |
| Width | 0.63 in (15.9 mm) |
| Depth | 0.38 in (9.7 mm) |
| Net Weight | 0.00 lb(US) (0.002 kg) |

Environment

| | |
|---------------------------------------|---|
| Fire resistance | 1202 °F (650 °C) / 30 s NF C 20-455 |
| Flame retardance | Self-extinguishing conforming to UL 94 V2 |
| Ambient Air Temperature for Operation | -40...185 °F (-40...85 °C) |

Ordering and shipping details

| | |
|-----------------------|-------------------------------------|
| Category | 80036-ENCLOSURE SYSTEMS ACCESSORIES |
| Discount Schedule | ES1 |
| GTIN | 3295150461093 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.07 oz (1.87 g) |
| Returnability | No |
| Country of origin | TW |

Packing Units

| | |
|------------------------------|-------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 1.57 in (4 cm) |
| Package 1 width | 5.12 in (13 cm) |
| Package 1 Length | 6.89 in (17.5 cm) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 100 |
| Package 2 Weight | 6.60 oz (187.0 g) |
| Package 2 Height | 1.57 in (4 cm) |

| | |
|------------------|-------------------|
| Package 2 width | 5.12 in (13 cm) |
| Package 2 Length | 6.89 in (17.5 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|