


Specification Sheet

Part Number: 151-10905



2- or 4-way entry options for the Q Tie, offering flexibility and stability

Q Tie Mount with Adhesive, 1.2" x 1.2" x 0.21", 4 way entry for Q18 thru Q50 ties, PA66, White, 100/bg

Article Number	151-10905
----------------	-----------

Type	QM30A
------	-------

Color	Natural (NA)
-------	--------------

Quantity Per	bag
--------------	-----

Product Description	Q Mounts are designed to work exclusively with the Q Tie cable tie series. This mounting component is available with adhesive or can be secured with screws. The Q Mount allows either a 2- or 4-way entry for the Q Tie, providing a quick and simple insertion into the mount. Once in place, the Q Tie will not slip out, even in vertical mounting applications.
---------------------	--

Short Description	Q Tie Mount with Adhesive, 1.2" x 1.2" x 0.21", 4 way entry for Q18 thru Q50 ties, PA66, White, 100/bg
-------------------	--

Global Part Name	QM30A-PA66-NA
Length L (Imperial)	1.2
Length L (Metric)	30.0
Fixation Method	Screw Mounting and Adhesive
Width W (Imperial)	1.2
Width W (Metric)	30.0
Height H (Imperial)	0.21
Height H (Metric)	4.5
Cable Tie Width Max (Imperial)	0.2
Cable Tie Width Max (Metric)	5.1
Mounting Hole Diameter D (Imperial)	0.16
Mounting Hole Diameter D (Metric)	4.1 mm
Mounting Hole Diameter D Min (Imperial)	0.16
Mounting Hole Diameter D Max (Metric)	4.1
Mounting Hole Centers (Imperial)	0.83

Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Adhesive	Synthetic rubber with base of polyethylene foam
Flammability	UL 94 V-2 (excluding adhesive)
Halogen Free	Yes
UV Resistant (Yes/No)	No
Adhesive Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Operating Temperature	-40°F to +140°F (-40°C to +60°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global

customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin.
(www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)