







P.C.B LAYOUT

Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:1A AC/DC
额定电流：1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压：300V AC/分钟
Temperature range:-40℃-+105℃
温度范围：-40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻：≥500MΩ
Contact resistance:≤20mΩ
接触电阻：≤20mΩ
Material:PA6T UL94V-0
材质：PA6T UL94V-0
Plating Category:1U"Gold
镀层：1U"Gold
Reflow soldring temperature:255±5℃，10S
回流焊温度：255±5℃，10S

X1321	W	V - 2x38	J - C40	D18
①	② ③	④	⑤ ⑥	⑦

1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Strighr 180°
4.Row No.Pin No:2xXX-2x01~2x40Pin
5.Plastic Height:J=1.0mm
6.Pin Length:C=4.0mm
7.Pin Length:D=1.8mm

X1321WV-2x38J-C40D18	PA6T	Brass	X1321F
PART N0	Material	Material(Pin)	Suitable XKB Female

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN		VIEW:	PART NO.: X1321WV-2x38J-C40D18
CHKD		UNIT: mm/in	DWG NO.: X-X1321WV-2x38J-C40D18
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0