

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: North American Power CABLE SJT 16/3 105°C BLACK	
	Model No. Power Cord	
	Part No./Ordering No. H-115-BK	Rev B

In Addition to GlobTek Inc.'s renewed ISO9001:2008 - Quality Management System Certification, GlobTek Inc. is now certified to:

- ISO13485:2003 - Medical Devices Quality Management System Certification
- ISO14001:2004 - Environmental Management System Certification

ISO Certificates are available online at <http://www.globtek.com/iso-certificates/>

The acceptance of this specification and use of the product described in this document indicates the acceptance and binding of the customer to Globtek TERMS AND CONDITIONS (attached to the end of this document), which supersede all other agreements, terms, and conditions (<http://en.globtek.com/terms-and-conditions/>).

Prop 65 Statement: <https://en.globtek.com/prop-65-statement.pdf>

Footnote:

GlobTek Inc. will not be liable for the safety and performance of these power supplies if unauthorized access and repair occurs. End user should consult applicable UL, CSA or EN standards for proper installation instruction.

Limitation of Use:

GlobTek products are intended for use with commercial, medical, and/or industrial equipment only. GlobTek product are not authorized for use as mission critical components in life support hazardous environment, nuclear or aircraft applications without prior written approval from the CEO of GlobTek Inc.

Contents of this document are subject to change without prior notice.

Customer Approval of Specification:

Please approve, sign and send back to GlobTek so we can complete order processing.
 A delay in receipt of this form will delay delivery schedule.

Company Name:	Customer P/N:
Quote Number:	Date:
Authorized Representative Name:	Authorized Representative Signature:

GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: North American Power CABLE SJT 16/3 105°C BLACK	
	Model No. Power Cord	Part No./Ordering No. H-115-BK
		Rev B

REVISION HISTORY

REV	DESCRIPTION	SUB	DATE	APPROVED
B	UPDATED UNIT OF MEASURE AND ADDED PACKAGING DETAILS	DR	06/02/2023	QA
A	Initial release	QA	12/02/2022	QA

AGENCY ONLINE DOCUMENTS


http://en.globtek.com/cordsets/
https://www.globtek.com/pdf/rohs_cert/01t30000002p8yCAAQ
https://www.globtek.com/pdf/iso_certificates/REACH.pdf
https://www.globtek.com/pdf/conflict-minerals.pdf
https://en.globtek.com/prop-65-statement.pdf

IPXY rating is based on 3rd party testing and customers should check suitability and test system level IPXY rating before ordering.

<p>GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111</p>	Drawing Title: North American Power CABLE SJT 16/3 105°C BLACK	
	Model No. Power Cord	
	Part No./Ordering No. H-115-BK	Rev B

Conductor:

Bare Copper; Cover: PVC SJT 16AWG*3C 105°C, core color: black, green, white, jacket: black color, environmentally friendly material



Note:


- Conductor construction: 26/0.254±0.005
 - Insulation outer diameter: Ø3.0±0.05
 - Insulation Thickness: Minimum 0.69mm:
 - Coating outer diameter: Ø8.3±0.15
 - Coating Thickness: Minimum 0.61mm
- unit of measure is feet fo ordering is in FEET

Printed on the wire is:

(UL) Exxxxxx SJT 105°C 3X16AWG (1.31mm²) 300V VW-1 (MFG Name, GlobTek, Inc. or equal)
CSA LLxxxxxx (or cUL) TYPE SJT 105°C 3X1.31mm²(16AWG) 300V VW-1

Packing:

Approximate 4000 meter per spool



GlobTek, Inc. www.globtek.com 186 Veterans Drive, Northvale, NJ 07647 Tel. (201) 784-1000 Fax (201) 784-0111	Drawing Title: North American Power CABLE SJT 16/3 105°C BLACK	
	Model No. Power Cord	Part No./Ordering No. H-115-BK
		Rev B

PACKAGING

Packing Spec P/N:

Box Qty: 1

Gift Box Size (mm):

Gift Box Color: White

Master Carton Size (mm): TBD

Master Carton Cubic Volume (m³): 0.00

Master GW (Kg): kg

wt Ea. (Kg): kg

wt Ea. (Kg): kg

LABEL SPECS: ,

PACK SPEC: