

## Specification Sheet

Part Number: WSM60IMHSUVH1

Design makes installation along frame rails fast and easy  
Using weld stud eliminates the need for grinding down painted surfaces  
which saves time

Weld Stud eliminates need for stocking multiple sized metal P-Clamps  
which saves time and cost



Weld Stud Mount, Max Bundle Diameter 6.0", Stud Diameter .24", PA66HIRHSUV, Black, 500/pkg

Article Number 151-00146

Type WSM60

Color Black (BK)

Quantity Per bag

Product Description When used in conjunction with a cable tie, the Weld Stud Mount significantly reduces time and labor, and eliminates the need for multiple sized P-clamps, nuts, and bolts. Simply weld the stud to the surface of any painted frame rail, and begin bundling with HellermannTyton cable ties. This eliminates the need in having to grind the surface in preparation. Adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T250, T255 and Wide Strap Cable Ties.

Short Description Weld Stud Mount, Max Bundle Diameter 6.0", Stud Diameter .24", PA66HIRHSUV, Black, 500/pkg

Global Part Name	WSM60-PA66HIRHSUV-BK
Length L (Imperial)	1.32
Length L (Metric)	33.5
Width W (Imperial)	1.07
Width W (Metric)	27.2
Height H (Imperial)	1.06
Height H (Metric)	27.0
Cable Tie Width Max (Imperial)	0.51
Cable Tie Width Max (Metric)	13.0
Stud Diameter (Metric)	6.0 mm
Stud Diameter (Imperial)	0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)