

2.4 GHz-2.5 GHz / 5.1 GHz-7.1 GHz, 2.5-3.5 dBi WiFi 6e Tilt and Swivel Rubber Duck Antenna - Reverse Polarity SMA (RP-SMA) Male Connector

## **HG247103RD-RSP**

#### **Features**

- · Tilt and Swivel Design
- · 2.4 GHz, 5 GHz, 6 GHz and 7 GHz Bands

- · Reverse Polarity SMA (RP-SMA) Male Connector
- 2.5 to 3.5 dBi Gain

### **Applications**

- Infotainment Systems, Routers, WiFi Hotspots, HD Video Trans Connected Cars or Self-Driving Cars, Fleet Management, Logismission, Gateways, Dash Cameras, Public Transportation
- WiFi 6e (802.11ax) Networks

- · IoT, Cellular, Zigbee, Z-Wave, Bluetooth

## Description

The L-com HG247103RD-RSP WiFi 6e Rubber Duck Antenna is a high performance, compact designed for 2.4, 5, 6 and 7 GHz bands. This tilt and swivel rubber duck antenna is available to ship the same day. It features a Reverse Polarity SMA (RP-SMA) Male Connector. The HG247103RD-RSP can be used on all consumer radios that have Reverse Polarity SMA connections. This RP-SMA rubber duck is suitable for WiFi Hotspots (IEEE 802.11ax/ac/n/b/g) as well as IoT, Zigbee and Bluetooth.

The high performance HG247103RD-RSP from L-com provides 3 dBi of gain and broad coverage. This WiFi 6e 2400 to 7125 MHz rubber duck antenna, as well as our wide selection of superior quality RF parts, ships same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other L-com products.

# Configuration

Design **Band Type** Radiation Pattern Wavelength Polarization

Connector Type

Portable Single Omni Directional

1/2 Vertical

SMA Male Reverse Polarity

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,400		7,125	MHz
Input VSWR		1.4:1	1.7:1	
Impedance		50		Ohms
Gain		3		dBi
Gain	2.6			dBi
Input Power			5	Watts

#### **Mechanical Specifications**

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 2.4 GHz-2.5 GHz / 5.1 GHz-7.1 GHz, 2.5-3.5 dBi WiFi 6e Tilt and Swivel Rubber Duck Antenna - Reverse Polarity SMA (RP-SMA) Male Connector



2.4 GHz-2.5 GHz / 5.1 GHz-7.1 GHz, 2.5-3.5 dBi WiFi 6e Tilt and Swivel Rubber Duck Antenna - Reverse Polarity SMA (RP-SMA) Male Connector

# **HG247103RD-RSP**

## **Environmental Specifications**

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

2.4 GHz-2.5 GHz / 5.1 GHz-7.1 GHz, 2.5-3.5 dBi WiFi 6e Tilt and Swivel Rubber Duck Antenna - Reverse Polarity SMA (RP-SMA) Male Connector from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

# **L-com CAD Drawing**

