

Important Note

If you need to connect a Cisco device to a newer laptop that doesn't have an RJ45 network port, we recommend U209-006-RJ45-X USB to RJ45 Cisco Serial Rollover Cable.

Cisco Console Rollover Cable (RJ45 M/M), 6 ft. (1.83 m)

MODEL NUMBER: **N205-006-BL-FCR**



Connects your computer or laptop to a Cisco router, server, switch or other Cisco networking equipment.

Features

Connects Your Computer or Laptop to a Cisco Networking Device

- Direct replacement for lost or damaged Cisco rollover cable
- Ideal for routers, servers, switches and other Cisco networking equipment
- Male RJ45 connectors
- 32 AWG copper wire
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332194183
Technology	Cat6
PHYSICAL	
Color	Blue
Cable Jacket Color	Blue
Cable Jacket Material	PVC

Highlights

- Direct replacement for existing Cisco rollover cable
- Works with new and old Cisco equipment
- 32 AWG copper wire
- Rugged PVC jacket
- Male RJ45 connectors

System Requirements

- Computer or laptop with RJ45 port
- Cisco networking hardware with RJ45 console port

Package Includes

- N205-006-BL-FCR Cisco Console Rollover Cable (RJ45 M/M), 6 ft.

Cable Shielding	UTP
Number of Conductors	4 Pair
Conductor Material	Stranded Copper
Conductor Gauge	32 AWG
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Cable Length (cm)	182.9
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.14
Shipping Weight (kg)	0.06
COMMUNICATIONS	
Bandwidth per TIA Standard	250 MHz
Maximum Data Rate	1 Gbps
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side A - Connector 2	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Connector Type	Molded; Rollover
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.