



Product: [8520](#)

Lead Wire, #14 Str TC, PVC Ins, TYPE MW MIL-W-76C-PVC

[Request Sample](#)

Product Description

Low Temp Plastic Lead Wire, 14AWG (41x30) Tinned Copper, PVC Insulation, TYPE MW MIL-W-76C-PVC 1000V 80C

Technical Specifications

Product Overview

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, (Type MW) MIL-W-76C-Low Temp applications
------------------------	---

Construction Details

Conductor

Size	Stranding	Material
14	41x30	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter
PVC - Polyvinyl Chloride	0.019 in (0.48 mm)	0.111 in (2.82 mm)

Overall Cable Diameter (Nominal):	0.111 in (2.82 mm)
-----------------------------------	--------------------

Electrical Characteristics

Voltage

UL Voltage Rating
1000 V RMS

Mechanical Characteristics

Bulk Cable Weight:	16 lbs/1000ft (24 kg/km)
--------------------	--------------------------

Standards and Compliance

Sustainability:	CA Prop 65
Military Compliance:	MIL-W-76C Type MWP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.395 Revision Date: 05-05-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8520 010100	Black	Reel	100 ft	612825210788	
8520 0101000	Black	Reel	1,000 ft	612825210795	P
8520 013100	Blue, Dark	Reel	100 ft	612825210801	
8520 006100	Blue, Light	Reel	100 ft	612825210733	
8520 0061000	Blue, Light	Reel	1,000 ft	612825210740	P
8520 001100	Brown	Reel	100 ft	612825210658	

8520 0011000	Brown	Reel	1,000 ft	612825210665	P
8520 005100	Green, Dark	Reel	100 ft	612825210719	
8520 0051000	Green, Dark	Reel	1,000 ft	612825210726	P
8520 003100	Orange	Reel	100 ft	612825210696	
8520 0031000	Orange	Reel	1,000 ft	612825210702	P
8520 002100	Red	Reel	100 ft	612825210672	
8520 0021000	Red	Reel	1,000 ft	612825210689	P
8520 009100	White	Reel	100 ft	612825210764	
8520 0091000	White	Reel	1,000 ft	612825210771	P
8520 0181000	White, Blue Stripe	Reel	1,000 ft		A

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.