

SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole



RF Connectors Technical Data Sheet

PE4980

Configuration

- SC Female Connector
- MIL-STD-348
- •50 Ohms
- Straight Body Geometry

Features

- Silver Plated Contact
- Hermetically Sealed

Contact plating according to QQ-S-365

Eyelet Interface Type

Solder Attachment

Bulkhead

Applications

• General Purpose Test

Rack and Panel Mount Applications

Description

Pasternack's PE4980 SC female bulkhead mount hermetically sealed connector solder attachment eyelet terminal, .655 inch D hole is part of our full line of RF components available for same-day shipping. This SC bulkhead connector allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Our SC female bulkhead connector PE4980 datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right connector for the job. Pasternack can also expertly build your custom cable connector assemblies for you and ship same-day.

Mechanical Specifications

Size

Length 1.47 in [37.34 mm]
Width/Dia. 0.96 in [24.38 mm]
Weight 0.116 lbs [52.62 g]

Material Specifications

| Description | Material | Plating |
|-------------|----------|--------------------|
| Contact | | Silver QQ-S-365 |
| Body | Brass | Nickel QQ-N-290 |
| | | |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole PE4980

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole



RF Connectors Technical Data Sheet

PE4980

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole PE4980

URL: https://www.pasternack.com/sc-female-standard-eyelit-terminal-connector-pe4980-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE4980 CAD Drawing

SC Female Bulkhead Mount Hermetically Sealed Connector Solder Attachment Eyelet Terminal, .655 inch D Hole

