

Precision SMA Female to SMA Female Adapter, 27 Ghz



RF Adapters Technical Data Sheet

PE91549

Configuration

- SMA Female Connector 1
- SMA Female Connector 2
- •50 Ohm

- Precision Design
- Straight Body Geometry

Features

• Max VSWR of 1.2:1 up to 27 GHz

Applications

• General Purpose Test

Precision Test & Measurement

Description

Pasternack's PE91549 SMA female to SMA female adapter is part of our full line of RF components available for same-day shipping. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our SMA to SMA adapter has a female to female gender configuration in a precision design. PE91549 SMA female to SMA female adapter operates to 27 GHz. The Pasternack RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters are often used to enable connections between two connector types that would otherwise not mate. Certain adapter configurations can also be used to protect connectors on expensive equipment where the number of connect/disconnect cycles is high. An RF, microwave or millimeter wave adapter is connected to the equipment, and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Pasternack also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		27	GHz
VSWR			1.2:1	

Mechanical Specifications

Size

 Length
 0.5 in [12.7 mm]

 Width
 0.25 in [6.35 mm]

Description	Connector 1	Connector 2
Туре	SMA Female	SMA Female
Polarity	Standard	Standard

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Precision SMA Female to SMA Female Adapter, 27 Ghz PE91549

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



Precision SMA Female to SMA Female Adapter, 27 Ghz

RF Adapters Technical Data Sheet

PE91549

Compliance Certifications (see product page for current document)

Precision SMA Female to SMA Female Adapter, 27 Ghz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Precision SMA Female to SMA Female Adapter, 27 Ghz PE91549

URL: https://www.pasternack.com/sma-female-sma-female-straight-adapter-pe91549-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

