

WE310F5

Wi-Fi 802.11 b/g/n BLE5

Product Description

The WE310F5 is a fully integrated, single-band Wi-Fi (802.11 b/g/n) and Bluetooth Low Energy (BLE5) combination module that provides a low-cost and highspeed wireless connection to an embedded microcontroller over UART, SPI and SDIO interfaces.

The comprehensive software features exposed through AT commands enable faster time to market, even with limited wireless expertise. IoT devices integrating WE310F5 are secured with WPA3 protocol, the nextgeneration, cutting-edge Wi-Fi security specification. Out-of-the-box support for Firmware Over-the-Air (FOTA) upgrades significantly reduces integration time. WE310F5 also offers multiple provisioning schemes, helping configure the device securely from a smartphone or a laptop.



Key Features

- Fully integrated, single-band Wi-Fi (11n) and BLE5 combination IoT module
- Low-cost, high-speed, serial-to-wireless connection to an MCU over UART, SPI and SDIO interface
- Comprehensive software features
- Low power consumption
- Advanced security features (including WPA3)
- Industrial-grade temperature range (-40 °C to +85 °C)
- Variants with (WE310F5-I) and without (WE310F5-P) antennas

Target Applications

Industrial/Commercial IoT

- Industrial automation
- Sensor gateways
- Condition-based monitoring
- Security panel
- Energy management
- Inspection camera
- Data logger
- Building automation

Smart Home

- Thermostat
- Air purifier
- Air conditioner
- Security/monitoring camera
- Pet food dispenser

AVAILABLE FOR

North A	merica	a	
EMEA			
Japan			
Austral	ia		
China*			
Korea*			
Taiwan'	¢.		
Brazil*			

Complete, Ready-to-Use Access to the Internet of Things



1



WE310F5

Module Wireless Specification	Wi-Fi: 802.11 b/g/n (2.4GHz) BLE-5	
Solution Architecture	Hosted (AT commands) Standalone (host-less)	
Host Interface	UART, SPI & SDIO	
Wi-Fi Modes	AP (access point) 14 STA (clients) Concurrent Mode (AP + STA) Wi-Fi Direct (P2P)*	
BLE Modes	Central Peripheral Concurrent	
Security Features	WPA/WPA2 (personal) WPA3 (personal) WPA3 (enterprise)* HTTPS server & client TLS-1.2/TLS-1.3*	
Coexistence	Inbuilt Wi-Fi BLE	
Provisioning (Through web-apps and native apps)	BLE enabled Wi-Fi HTTPS enabled Wi-Fi	
Cloud Agent	Amazon AWS loT* Microsoft Azure*	
Wi-Fi Throughput	25 Mbps	
Firmware Upgrade	FOTA	
Dimension	Integrated antenna (WE310F5-I): 18 x 15 mm (LGA package) External antenna (WE310F5-P): 14.3 x 13.1 mm (LGA package)	
Wi-Fi Tx output power	18 dBm	
BLE Tx output power	8 dBm	
Operating Temperature	-40 °C to +85 °C (industrial grade)	
Operating Voltage	3.3 V Тур	
Compliance	Wi-Fi Alliance BT-SIG	*Natavailabla in first release

*Not available in first release

QUESTIONS? VISIT WWW.TELIT.COM/CONTACT-US

🚯 www.telit.com/facebook 🔰 🝈 www.telit.com/linkedin | 👩 www.telit.com/twitter

Telit reserves all rights to this document and the information contained herein. Products, names, logos and designs described herein may in whole or in part be subject to intellectual property rights. The information contained herein is provided "as is." No warranty of any kind, either express or implied, is made in relation to the accuracy, reliability, fitness for a particular purpose or content of this document. This document may be revised by Telit at any time. For most recent documents, please visit www.telit.com



[02.2022]