REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.12.5	阿树



Specifications:
规格：
Voltage rating:400V AC/DC
额定电压：400V AC/DC
Current rating:14A AC/DC
额定电流：14A AC/DC
Withstanding voltage:1800V AC/minute
耐受电压：1800V AC/分钟
Temperature range:−40℃−+125℃
温度范围：−40℃−+125℃
Insulation resistance:1000MΩ min
绝缘电阻：1000MΩ Min
Contact resistance:10mΩ Max
接触电阻：10mΩ Max

PART NO.:

X3501 H−02 B−N0
① ② ③ ④ ⑤

①Series No
②Category:H−HSG
③Row No.Pin No:XX−02~12P
④Category:
A:TPA Type, A KEY Black
B:TPA Type, B KEY Nature
A0:Standard , A KEY Black
B0:Standard , B KEY Nature
⑤Material:N0−Nylon UL94V−0

Poles	Dimensions	
	A	B
02	3.50	8.00
03	7.00	11.50
04	10.50	15.00
05	14.00	18.50
06	17.50	22.00
07	21.00	25.50
08	24.50	29.00
12	38.50	43.00

PART N0	Material	Category	Suitable XKB Wafer	Suitable XKB Terminal	Category
X3501H−02B−N0	Nylon	H−XXA / H−XXA0	X3501W−A	X3501T	X3501HL
		H−XXB / H−XXB0	X3501W−B		

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB Connection 星创

DESIGN	阿树	VIEW:	MODEL TYPE: 3.5mm Crimp Style Connector
CHECKED		UNIT: mm/in	PART NO.: X3501H−02B−N0
APPROVED		SIZE: A4	DWG NO.: X−X3501H−02B−N0

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1