

Data sheet

3757.3 ZAP SR OG



End plate, Width: 1.5 mm, Colour: Orange

Business data

Article number	3757.3
Article name	ZAP SR OG
GTIN (EAN)	4044211060718
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	1.8 g
Weight per piece (including packaging)	1.9 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	3757.2
Product description	End plate

Data sheet

3757.3 ZAP SR OG

Technical data

Dimensions

Length	40 mm
Width	1.5 mm
Height	287 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3584.2</u>	ZSLN 2,5/2A GNYE	4044211151881	100 ST



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1709.2</u>	ZSLN 2,5/2A/15 Ex GNYE	4044211059385	100 ST



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1711.2</u>	ZSLN 2,5/2A Ex GNYE	4044211059347	100 ST



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3586.2</u>	ZSLN 2,5/2A/15 GNYE	4044211151935	100 ST



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1700.2</u>	ZSRK 2,5/2A/15 Ex BG	4044211059354	100

Data sheet

3757.3 ZAP SR OG

##INVERSE##CONTA-CONNECT




Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1702.2</u>	ZSRK 2,5/2A Ex BG	4044211059316	100



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3583.2</u>	ZSRK 2,5/2A BG	4044211151874	100



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3585.2</u>	ZSRK 2,5/2A/15 BG	4044211151904	100