

MKKDS 3/ 2-5,08-EX - PCB terminal block



1760581

<https://www.phoenixcontact.com/us/products/1760581>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PCB terminal block, number of positions per row: 2, product range: MKKDS 3-EX, pitch: 5.08 mm, screw head form: L Slotted, color: green, Pin layout: Linear pinning, Solder pin [P]: 5 mm, type of packaging: packed in cardboard

Commercial data

Item number	1760581
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AA13
Product key	AAMFKA
GTIN	4046356368292
Weight per piece (including packing)	9.622 g
Weight per piece (excluding packing)	9.592 g
Customs tariff number	85369010
Country of origin	CN

MKKDS 3/ 2-5,08-EX - PCB terminal block



1760581

<https://www.phoenixcontact.com/us/products/1760581>

Technical data

Product properties

Type	PC terminal block can be aligned
Product type	Printed circuit board terminal
Product family	MKKDS 3-EX
Number of positions	2
Pitch	5.08 mm
Pin layout	Linear pinning

Electrical properties

Rated voltage (II/2)	630 V
Rated voltage (III/2)	400 V
Rated surge voltage (II/2)	4 kV
Rated surge voltage (III/2)	4 kV
Rated surge voltage (III/3)	4 kV

Mounting

Mounting type	Wave soldering
Pin layout	Linear pinning
Drive form screw head	Slotted (L)
Connection method	Screw connection with tension sleeve
Drive form screw head	Slotted (L)

Material specifications

Contact surface	Tin Sn
-----------------	--------

Dimensions

Width	12.7 mm
Height	36.5 mm
Installed height	31.5 mm
Length of the solder pin	5 mm
Length	22.3 mm
Length of the solder pin	5 mm
Hole diameter	1.3 mm
Pitch	5.08 mm

PCB design

Pin spacing	15.24 mm
-------------	----------

Packaging specifications

Type of packaging	packed in cardboard
-------------------	---------------------

MKKDS 3/ 2-5,08-EX - PCB terminal block



1760581

<https://www.phoenixcontact.com/us/products/1760581>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1760581>



ATEX

Approval ID: KEMA 01ATEX2130 U



IECEx

Approval ID: IECEx KEM 07.0019 U



EAC Ex

Approval ID: B.00065/19

MKKDS 3/ 2-5,08-EX - PCB terminal block



1760581

<https://www.phoenixcontact.com/us/products/1760581>

Classifications

ECLASS

ECLASS-11.0	27460101
ECLASS-12.0	27460101
ECLASS-13.0	27460101

ETIM

ETIM 9.0	EC002643
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

MKKDS 3/ 2-5,08-EX - PCB terminal block



1760581
<https://www.phoenixcontact.com/us/products/1760581>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com