


# Data sheet

## 2003.2 TRS 1 BG



Insulation plate, Colour: Beige

### Business data

Article number	2003.2
Article name	TRS 1 BG
GTIN (EAN)	4044211048068
Packaging unit	100
Quantity unit	PC
Weight per piece (not including packaging)	0.2 g
Weight per piece (including packaging)	0.21 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2003.2
Product description	Insulation plate

# Data sheet

## 2003.2 TRS 1 BG



### Technical data

#### Dimensions

Length	26 mm
Width	19.5 mm
Height	0.6 mm

#### Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

#### Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----


---

**Media**

---


### Accessories

#### ##INVERSE##CONTA-CONNECT



Feed-through terminal, Faston Spade connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1014.2</u>	FF 2,5 BG	4044211003203	100



Feed-through terminal, Faston Spade connection / screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1019.2</u>	SF 2,5-4 BG	4044211004323	100 ST




Four-wire motor-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm², Colour: Multi-coloured

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1521.2</u>	VMAB 2,5-4	4044211046682	10 ST



Five-wire mains-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm², Colour: Multi-coloured


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1524.2</u>	FNAB 2,5-4	4044211046781	10 ST



Five-wire mains-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Colour: Multi-coloured

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1525.2</u>	FNAB 6-10	4044211046804	10 ST

### ##INVERSE##CONTA-CONNECT



Four-wire motor-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Colour: Multi-coloured

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1522.2</u>	VMAB 6-10	4044211046699	10 ST




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1134.2</u>	PTK 10/DU BG	4044211020293	50 ST




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1130.2</u>	PTK 10/LT BG	4044211019853	50 ST




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1131.2</u>	PTK 10/LT/STB BG	4044211019969	50 ST



Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1132.2</u>	PTK 10/QT BG	4044211020071	50 ST



Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm², Width: 8 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1133.2</u>	PTK 10/QT/STB BG	4044211020187	50 ST

### ##INVERSE##CONTA-CONNECT




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1135.2</u>	PTK 10/DU/STB BG	4044211020408	50 ST




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17366.2</u>	PTK 10/LT/HB BG	4044211185145	50 ST




Test disconnect terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17367.2</u>	PTK 10/LT/STB/HB BG	4044211185152	50 ST




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1168.2</u>	RK 6-10/35/SAS BG	4044211128630	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1001.2</u>	RK 2,5-4 BG	4044211000240	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Black-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1563.2</u>	RK 2,5-4/PE BKYE	4044211047344	100 ST

# Data sheet


## 2003.2 TRS 1 BG

### ##INVERSE##CONTA-CONNECT




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1748.4</u>	RK 2,5-4 PA-G BK	4044211141134	100 ST




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1167.2</u>	RK 2,5-4/35/SAS BG	4044211128623	100




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1211.2</u>	RK 2,5-4/ZRL BG	4044211028558	100




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1005.2</u>	RK 6-10 BG	4044211001148	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1210.2</u>	RK 2,5-4/ZR BG	4044211028459	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 4 mm<sup>2</sup>, Width: 6 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1577.2</u>	RK 2,5-4/35 BG	4044211047566	100

### ##INVERSE##CONTA-CONNECT



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Black-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1564.2</u>	RK 6-10/PE BKYE	4044211047351	100 ST



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1578.2</u>	RK 6-10/35 BG	4044211047627	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1749.4</u>	RK 6-10 PA-G BK	4044211141141	100 ST