

Test adapter, Length: 37.3 mm, Pitch size: 5 mm, Colour: Beige

Business data

Article number	2812.0
Article name	TA 5/1/ST
GTIN (EAN)	4044211055394
Packaging unit	10
Quantity unit	PC
Weight per piece (not including packaging)	4.77 g
Weight per piece (including packaging)	4.8 g
Unit of weight	G
Customs number	85369010
Country of origin	DE
Product description	Test adapter
Colour	Beige



### Technical data

#### Dimensions

Length	37.3 mm
Additional height for each terminal block	35.5 mm
Pitch size	5 mm

#### Connection data

Wire cross-section stranded, min.	0.5 mm <sup>2</sup>
Wire cross-section stranded, max.	1 mm <sup>2</sup>
Stripping length	5 mm

#### Materials

Insulation housing	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

#### Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes



---


**Media**

---



### Accessories

#### Terminal blocks




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1296.2</u>	RK 2,5 BG	4044211040215	100




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 25 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1166.2</u>	RK 2,5/SAS BG	4044211128616	100



Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1426.2</u>	RK 2,5 Ex BG	4044211044718	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 25 mm², Width: 5 mm, Colour: Black-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1562.2</u>	RK 2,5/PE BKYE	4044211047337	100 ST

#### Quick marking



Terminal marker / Pocket Maxicard, Length: 5 mm, Width: 5 mm, Colour: White

Article number	Article name	GTIN (EAN)	Packaging unit
<u>4600.7</u>	PMC SB 5/50 WH	4044211088903	500 ST

##INVERSE##CONTA-CONNECT





Four-wire motor-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm<sup>2</sup>, Colour: Multi-coloured

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1520.2</u>	VMAB 2,5	4044211046613	10 ST




Five-wire mains-connection block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm<sup>2</sup>, Colour: Multi-coloured

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1523.2</u>	FNAB 2,5	4044211046729	10 ST




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 25 mm<sup>2</sup>, Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1166.2</u>	RK 2,5/SAS BG	4044211128616	100




Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 10 mm<sup>2</sup>, Width: 8 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1430.2</u>	RK 6-10 Ex BG	4044211044770	100



Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm<sup>2</sup>, Width: 12 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1431.2</u>	RK 16 Ex BG	4044211044787	50



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 25 mm<sup>2</sup>, Width: 5 mm, Colour: Beige


Article number	Article name	GTIN (EAN)	Packaging unit
<u>1166.2</u>	RK 2,5/SAS BG	4044211128616	100






Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm<sup>2</sup>, Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1431.2</u>	RK 16 Ex BG	4044211044787	50




Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1426.2</u>	RK 2,5 Ex BG	4044211044718	100



Ex feed-through terminal ATEX-certified, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 16 mm<sup>2</sup>, Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1431.2</u>	RK 16 Ex BG	4044211044787	50



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 25 mm<sup>2</sup>, Width: 5 mm, Colour: Black-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1562.2</u>	RK 2,5/PE BKYE	4044211047337	100 ST