


Data sheet

17022.2 TW 35-120/B/B BG



Partition plate, Width: 2 mm, Colour: Beige

Business data

Article number	<u>17022.2</u>
Article name	TW 35-120/B/B BG
GTIN (EAN)	4044211131678
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	21.6 g
Weight per piece (including packaging)	21.79 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	Partition plate
Colour	Beige

Technical data

Dimensions

Length	156 mm
Width	2 mm
Height	76 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-0
Working temperature, min.	-40 °C
Working temperature, max.	120 °C

Environmental Product Compliance


REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Media

Accessories


17022.2 TW 35-120/B/B BG

##INVERSE##CONTA-CONNECT




High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 120 mm², Width: 32 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17003.2</u>	HSK 120/M10 B BG	4044211131487	10 ST




High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 120 mm², Width: 32 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17004.2</u>	HSK 120/M12 B BG	4044211131494	10 ST




High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 50 mm², Width: 21 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17002.2</u>	HSK 50/M8 B BG	4044211131470	10 ST




High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 35 mm², Width: 16 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17005.2</u>	HSK 35/M6 B/B BG	4044211131500	10 ST



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 50 mm², Width: 21 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17006.2</u>	HSK 50/M8 B/B BG	4044211131517	10 ST




High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 120 mm², Width: 32 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17007.2</u>	HSK 120/M10 B/B BG	4044211131524	10 ST

Data sheet

17022.2 TW 35-120/B/B BG

##INVERSE##CONTA-CONNECT



High-power stud terminal, Stud connection, Mounting type: Mounting rail TS 35/7.5,
Rated cross-section: 120 mm², Width: 32 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>17003.2</u>	HSK 120/M10 B BG	4044211131487	10 ST