

# Data sheet

## 2136.5 EH 2 BU



End support, Mounting type: Mounting surface, Width: 7 mm, Colour: Blue

**RAL:** Ähnlich 5005

### Business data

|  |               |
|--|---------------|
| Article number                             | 2136.5        |
| Article name                               | EH 2 BU       |
| GTIN (EAN)                                 | 4044211049577 |
| Packaging unit                             | 50            |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 2.1 g         |
| Weight per piece (including packaging)     | 2.16 g        |
| Unit of weight                             | G             |
| Customs number                             | 85389099      |
| Country of origin                          | DE            |
| Prio-Article                               | 2136.2        |
| Product description                        | End support   |

# Data sheet

## 2136.5 EH 2 BU

---

### Technical data

---

#### Dimensions

|                |         |
|----------------|---------|
| Length         | 22 mm   |
| Width          | 7 mm    |
| Terminal width | 7.00 mm |
| Height         | 23 mm   |
| Hole diameter  | 3.5 mm  |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Flammability class UL 94  | V-2           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 105 °C        |

#### Further technical data

|               |               |
|---------------|---------------|
| Mounting type | Mounting face |
|---------------|---------------|

#### Environmental Product Compliance

|                                |    |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|

---

**Media**

---


### Accessories

#### ##INVERSE##CONTA-CONNECT




Ex feed-through terminal for direct mount ATEX-certified, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Width: 6 mm, Colour: Beige

| Article number | Article name  | GTIN (EAN)    | Packaging unit |
|----------------|---------------|---------------|----------------|
| <u>1406.2</u>  | BKA 4/1 Ex BG | 4044211044534 | 100            |



Ex feed-through terminal for direct mount ATEX-certified, Screw connection, Mounting type: Mounting surface, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

| Article number | Article name    | GTIN (EAN)    | Packaging unit |
|----------------|-----------------|---------------|----------------|
| <u>1405.2</u>  | BKA 2,5/1 Ex BG | 4044211044527 | 100            |



Feed-through terminal for direct mount, Screw connection, Mounting type: Mounting surface, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>1320.2</u>  | BKA 2,5/1 BG | 4044211042967 | 100            |



Feed-through terminal for direct mount, Screw connection, Mounting type: Mounting surface, Rated cross-section: 4 mm², Width: 6 mm, Colour: Beige

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>2158.2</u>  | BKA 4/1 BG   | 4044211049782 | 100            |