REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图片面升级整理图面	2024.08.03	阿 树





2方4圆



3方5圆





■SPECIFICATIONS
- •Voltage rating:600V AC/DC
- •Current rating:9A AC/DC
- •Withstanding Voltage:1500V AC/minute
- •Temperature range:−45°C+125°C
- •Insulation resistance:≥1000MΩ
- •Contact resistance:≤20mΩ





PART NO.:

X9357 H M−2x07−N0
① ② ③ ④ ⑤

① Series No.
② Category:H−HSG
③ Welding Board Angle:M−Male HGS
④ Row No.−Pin No.:2xXX−2x01P~2x10P,2x12P
⑤ Plug the Pin & special No:B−With the back seat
⑥ Material:N0−PA66 94V−0 White

Poles	Dimensions(mm)	
	A	B
2x01	5.40	
2x02	9.60	4.20
2x03	13.80	8.40
2x04	18.00	12.60
2x05	22.20	16.80
2x06	26.40	21.00
2x07	30.60	25.20
2x08	34.80	29.40
2x09	39.00	33.60
2x10	43.20	37.80
2x12	51.60	46.20

X9357HM−2x07−N0	PA66	X9357W−A	X9357HF
PART N0	Material	Suitable XBK Wafer	Suitable XBK Housing

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9357HM−2x07−N0
APPROVED		SIZE: A4	DWG NO.: X−X9357HM−2x07−N0

SCALE	PAGE	REVISION
N/A	1/1	A1