

# Data sheet

## 3788.8 ZAP 10/2A YE



End plate, Width: 2 mm, Colour: Yellow

RAL: 1026

### Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | 3788.8        |
| Article name                               | ZAP 10/2A YE  |
| GTIN (EAN)                                 | 4044211107956 |
| Packaging unit                             | 20            |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 4 g           |
| Weight per piece (including packaging)     | 4.25 g        |
| Unit of weight                             | G             |
| Customs number                             | 85389099      |
| Country of origin                          | DE            |
| Prio-Article                               | 3788.2        |
| Product description                        | End plate     |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Length | 73.5 mm |
| Width  | 2 mm    |
| Height | 42.7 mm |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Flammability class UL 94  | V-2           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 105 °C        |

#### Further technical data

|                       |   |
|-----------------------|---|
| Designed as end plate | ✓ |
| Snap-on available     | ✓ |

#### Environmental Product Compliance

|                                |    |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|

---

Media

---

### Accessories

#### ##INVERSE##CONTA-CONNECT



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Green-yellow

| Article number | Article name      | GTIN (EAN)    | Packaging unit |
|----------------|-------------------|---------------|----------------|
| <u>1726.2</u>  | ZSL 10/2A Ex GNYE | 4044211059583 | 50 ST          |



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Green-yellow

| Article number | Article name   | GTIN (EAN)    | Packaging unit |
|----------------|----------------|---------------|----------------|
| <u>3598.2</u>  | ZSL 10/2A GNYE | 4044211152000 | 50 ST          |



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Beige

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>3597.2</u>  | ZRK 10/2A BG | 4044211151997 | 50             |



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 10.1 mm, Colour: Beige

| Article number | Article name    | GTIN (EAN)    | Packaging unit |
|----------------|-----------------|---------------|----------------|
| <u>1720.2</u>  | ZRK 10/2A Ex BG | 4044211059569 | 50             |