


Data sheet

2890.5 HP DLIS BU



Retaining plate, Width: 1.5 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	2890.5
Article name	HP DLIS BU
GTIN (EAN)	4044211056155
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	4.3 g
Weight per piece (including packaging)	4.44 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	Fixing plate
Colour	Blue

Data sheet

2890.5 HP DLIS BU



Technical data

Dimensions

Length	93 mm
Width	1.5 mm
Height	52.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C


Environmental Product Compliance

REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Media


Accessories

##INVERSE##CONTA-CONNECT




Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 18 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2716.2</u>	DLIS 2,5 B-3L/N/PE BG	4044211129903	25 ST




Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 18 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1446.2</u>	DLIS 2,5 B-W BG	4044211044954	16 ST




Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 12 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1447.2</u>	DLIS 2,5 B-D BG	4044211044961	25 ST




Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 18 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2715.2</u>	DLIS 2,5 B-3L/3N/3PE BG	4044211129897	16 ST



Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 18 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2718.2</u>	DLIS 2,5 B-6L/3PE BG	4044211129927	16 ST




Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1410.2</u>	DLIS 2,5 PE/L/NT BG	4044211044558	50 ST

Data sheet

2890.5 HP DLIS BU

##INVERSE##CONTA-CONNECT



Three-wire installation terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 18 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2717.2</u>	DLIS 2,5 B-6L BG	4044211129910	16 ST