




End plate, Width: 2.7 mm, Colour: Black

RAL: 9005

Business data

Article number	2047.4
Article name	AP SI BK
GTIN (EAN)	4044211130183
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	4.76 g
Weight per piece (including packaging)	4.91 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2047.2
Product description	End plate

Data sheet

2047.4 AP SI BK

Technical data

Dimensions

Length	53.8 mm
Width	2.7 mm
Min. thickness	2.7 mm
Height	41.6 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT




Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1004.4</u>	SK 1/35 24V AC LED(RD) PA-G BK	4044211129989	20 ST




Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1119.4</u>	SK 1/35 48V AC LED(RD) PA-G BK	4044211130008	20 ST



Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1375.4</u>	SK 1/35 230V AC G PA-G BK	4044211129941	20 ST



Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1380.4</u>	SK 1/35 24V DC LED(RD) PA-G BK	4044211129972	20 ST



Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1367.4</u>	SK 1/35 PA-G BK	4044211128555	20 ST



Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1067.4</u>	SK 1/35 48V DC LED(RD) PA-G BK	4044211129996	20 ST

##INVERSE##CONTA-CONNECT



Fused terminal with screw cap for indicator fuses 5x25 mm, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1368.4</u>	SK 1/35 m.K. PA-G BK	4044211129811	20 ST



Fused terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 10 mm², Width: 12.2 mm, Colour: Black

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1376.4</u>	SK 1/35 115V AC G PA-G BK	4044211129958	20 ST