


Data sheet

2714.2 AP IKD 2,5/kurz BG



End plate, Colour: Beige

Business data

Article number	2714.2
Article name	AP IKD 2,5/kurz BG
GTIN (EAN)	4044211054557
Packaging unit	20
Quantity unit	PC
Weight per piece (not including packaging)	0.96 g
Weight per piece (including packaging)	1.05 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Product description	End plate
Colour	Beige

Technical data

Dimensions

Length	21.8 mm
--------	---------

Height	34.5 mm
--------	---------

Materials

Material	Polyamide 6.6
----------	---------------

Flammability class UL 94	V-2
--------------------------	-----

Working temperature, min.	-40 °C
---------------------------	--------

Working temperature, max.	105 °C
---------------------------	--------

Further technical data

Designed as end plate	✓
-----------------------	---

Snap-on available	✓
-------------------	---

Environmental Product Compliance

REACH Conform	yes
---------------	-----

REACH Reference date	2023-06-14
----------------------	------------


REACH Candidate Substance Note	No
--------------------------------	----

RoHS Conform	yes
--------------	-----

Media


Accessories

##INVERSE##CONTA-CONNECT




Three-level initiator terminal | Multi-wire terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2268.2</u>	IKD 2,5/Q BG	4044211050771	50




Three-level initiator terminal | Multi-wire terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1295.2</u>	IKD 2,5/F BG	4044211040093	50



Three-level initiator terminal | Multi-wire terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2269.2</u>	IKD 2,5/F/Q BG	4044211050795	50 ST



Three-level initiator terminal | Multi-wire terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1261.2</u>	IKD 2,5 BG	4044211035433	50