


# Data sheet

## 3757.8 ZAP SR YE



End plate, Width: 1.5 mm, Colour: Yellow

**RAL:** 1026

### Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | 3757.8        |
| Article name                               | ZAP SR YE     |
| GTIN (EAN)                                 | 4044211108342 |
| Packaging unit                             | 50            |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 1.8 g         |
| Weight per piece (including packaging)     | 1.9 g         |
| Unit of weight                             | G             |
| Customs number                             | 85389099      |
| Country of origin                          | DE            |
| Prio-Article                               | 3757.2        |
| Product description                        | End plate     |

# Data sheet

## 3757.8 ZAP SR YE

---

### Technical data

---

#### Dimensions

|        |        |
|--------|--------|
| Length | 40 mm  |
| Width  | 1.5 mm |
| Height | 287 mm |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Flammability class UL 94  | V-2           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 105 °C        |

#### Further technical data

|                       |   |
|-----------------------|---|
| Designed as end plate | ✓ |
| Snap-on available     | ✓ |

#### Environmental Product Compliance

|                                |    |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|

---

**Media**

---

### Accessories

#### ##INVERSE##CONTA-CONNECT



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name     | GTIN (EAN)    | Packaging unit |
|----------------|------------------|---------------|----------------|
| <u>3584.2</u>  | ZSLN 2,5/2A GNYE | 4044211151881 | 100 ST         |



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name           | GTIN (EAN)    | Packaging unit |
|----------------|------------------------|---------------|----------------|
| <u>1709.2</u>  | ZSLN 2,5/2A/15 Ex GNYE | 4044211059385 | 100 ST         |



Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name        | GTIN (EAN)    | Packaging unit |
|----------------|---------------------|---------------|----------------|
| <u>1711.2</u>  | ZSLN 2,5/2A Ex GNYE | 4044211059347 | 100 ST         |



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name        | GTIN (EAN)    | Packaging unit |
|----------------|---------------------|---------------|----------------|
| <u>3586.2</u>  | ZSLN 2,5/2A/15 GNYE | 4044211151935 | 100 ST         |



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

| Article number | Article name         | GTIN (EAN)    | Packaging unit |
|----------------|----------------------|---------------|----------------|
| <u>1700.2</u>  | ZSRK 2,5/2A/15 Ex BG | 4044211059354 | 100            |

# Data sheet

## 3757.8 ZAP SR YE

### ##INVERSE##CONTA-CONNECT




Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name      | GTIN (EAN)    | Packaging unit |
|----------------|-------------------|---------------|----------------|
| <u>1702.2</u>  | ZSRK 2,5/2A Ex BG | 4044211059316 | 100            |



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name   | GTIN (EAN)    | Packaging unit |
|----------------|----------------|---------------|----------------|
| <u>3583.2</u>  | ZSRK 2,5/2A BG | 4044211151874 | 100            |



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 15/5.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name      | GTIN (EAN)    | Packaging unit |
|----------------|-------------------|---------------|----------------|
| <u>3585.2</u>  | ZSRK 2,5/2A/15 BG | 4044211151904 | 100            |