

Data sheet

3702.5 ZAP 2,5/4A BU



End plate, Width: 2 mm, Colour: Blue

RAL: Ähnlich 5005

Business data

Article number	3702.5
Article name	ZAP 2,5/4A BU
GTIN (EAN)	4044211060114
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	3 g
Weight per piece (including packaging)	3.1 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	3702.2
Product description	End plate

Technical data

Dimensions

Length	83.6 mm
Width	2 mm
Height	30.8 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Designed as end plate	✓
Snap-on available	✓

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3512.2</u>	ZSL 2,5/4A GNYE	4044211058562	100 ST




Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Green-yellow

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1715.2</u>	ZSL 2,5/4A Ex GNYE	4044211058555	100 ST



Double-level terminal with electronic components, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3505.2</u>	ZRK 2,5/2x2A/LED1(RD)/24V DC BG	4044211058531	100 ST



Double-level terminal with electronic components, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3543.2</u>	ZRK 2,5/2x2A/LED2(RD)/24V DC BG	4044211058845	100 ST



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1706.2</u>	ZRK 2,5/4A Ex BG	4044211058463	100

##INVERSE##CONTA-CONNECT



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3503.2</u>	ZRK 2,5/2x2A BG	4044211058494	100



Double-level terminal with electronic components, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3504.2</u>	ZRK 2,5/2x2A/D1 BG	4044211058524	100 ST



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3502.2</u>	ZRK 2,5/4A BG	4044211151713	100



Double-level terminal with electronic components, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm², Width: 5.1 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>3542.2</u>	ZRK 2,5/2x2A/D2 BG	4044211058838	100 ST