



End stop, Mounting type: Mounting rail TS 35/7.5, Width: 7.5 mm, Colour: Beige

Business data

Article number	2005.2
Article name	ES 35 BG
GTIN (EAN)	4044211048082
Packaging unit	50
Quantity unit	PC
Weight per piece (not including packaging)	4.6 g
Weight per piece (including packaging)	4.7 g
Unit of weight	G
Customs number	85389099
Country of origin	DE
Prio-Article	2005.2
Product description	End bracket

Data sheet

2005.2 ES 35 BG

Technical data

Dimensions

Length	45.5 mm
Width	7.5 mm
Terminal width	7.50 mm
Height	31 mm
Height TS 35/7.5	31.5 mm

Materials

Material	Polyamide 6.6
Flammability class UL 94	V-2
Working temperature, min.	-40 °C
Working temperature, max.	105 °C

Further technical data

Mounting type	Mounting rail TS 35/7,5
Tightening torque, fastening screw max.	0.6 Nm
Tightening torque, fastening screw min.	0.5 Nm

Environmental Product Compliance

REACH Candidate Substance Note	No
--------------------------------	----

Media

Accessories

##INVERSE##CONTA-CONNECT




Screw-distributor block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and mounting surface, Rated cross-section of input: 16 mm², Rated cross-section of output: 16 mm², Colour: Light grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27207.0</u>	SVBKA 16 LG	4044211218423	10



Screw-distributor block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and mounting surface, Rated cross-section of input: 35 mm², Rated cross-section of output: 35 mm², Colour: Light grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27208.0</u>	SVBKA 35 LG	4044211218454	10




Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm², Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1001.2</u>	RK 2,5-4 BG	4044211000240	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 2.5 mm², Width: 5 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1030.2</u>	SRK 2,5 BG	4044211006723	100



Feed-through terminal, Screw connection, Mounting type: Mounting rail TS 35/7.5 and TS 32, Rated cross-section: 4 mm², Width: 6 mm, Colour: Beige

Article number	Article name	GTIN (EAN)	Packaging unit
<u>1015.2</u>	RK 1,5-4 BG	4044211003425	100


##INVERSE##CONTA-CONNECT



Screw-distributor block, Screw connection, Mounting type: Mounting rail TS 35/7.5 and mounting surface, Rated cross-section of input: 16 mm², Rated cross-section of output: 16 mm², Colour: Light grey

Article number	Article name	GTIN (EAN)	Packaging unit
<u>27207.0</u>	SVBKA 16 LG	4044211218423	10

Quick marking



Terminal marker / Pocket Maxicard, Length: 5 mm, Width: 6 mm, Colour: White

Article number	Article name	GTIN (EAN)	Packaging unit
<u>4702.7</u>	PMC SB 6/50 WH	4044211089986	500 ST



Terminal marker / Pocket Maxicard, Length: 10 mm, Width: 5 mm, Colour: White

Article number	Article name	GTIN (EAN)	Packaging unit
<u>9000.7</u>	PMC BSTR 5/36 WH	4044211091088	360 ST

Marker holder



Group marker holder, Width: 8.5 mm, Material: PA6.6

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2361.0</u>	SchT 7	4044211051501	100 ST



Group marker holder, Width: 8.5 mm, Material: PA6.6

Article number	Article name	GTIN (EAN)	Packaging unit
<u>2504.0</u>	SchT 7	4044211053048	100 ST