





Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:1A AC/DC
额定电流：1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压：300V AC/分钟
Temperature range:-40℃-+105℃
温度范围：-40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻：≥500MΩ
Contact resistance:≤20mΩ
接触电阻：≤20mΩ
Material:PA6T UL94V-0
材质：PA6T UL94V-0
Plating Category:1U"Gold
镀层：1U"Gold
Wave soldring temperature:255±5℃，10S
波峰焊温度：255±5℃，10S

X1311 F R - 21 - C43 D24
① ② ③ ④ ⑤ ⑥

1.Series No
2.Category:F-Female
3.Welding Board Angle:R-Stright 90°
4.Row No.Pin No:XX-01~40 Pin
5.Plastic height:C=4.3mm
6.Pin Length:D=2.4mm



PCB LAYOUT

X1311FR-21-C43D24	PA6T	Brass	X1311W
PART N0	Material	Material(Pin)	Suitable XKB Wafer

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

UNSPECIFIED TOLERANCES	
ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector
DWN		VIEW:	PART NO.: X1311FR-21-C43D24
CHKD		UNIT: mm/in	DWG NO.: X-X1311FR-21-C43D24
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0