


DS-PTIO 1,5/S - Cover segment



1045987

<https://www.phoenixcontact.com/us/products/1045987>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover segments, large segment: 32.25 x 13.83 x 0.9, small segment: 22.65 x 11.65 x 0.9, color: gray

Commercial data

Item number	1045987
Packing unit	50 pc
Sales key	BE29
Product key	BE2Z1X
Catalog page	Page 42 (C-1-2019)
GTIN	4055626640211
Weight per piece (including packing)	1.99 g
Weight per piece (excluding packing)	1.8 g
Customs tariff number	85369010
Country of origin	PL

DS-PTIO 1,5/S - Cover segment

1045987

<https://www.phoenixcontact.com/us/products/1045987>



Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	0.8 mm
End cover width	0.8 mm
Height	121.65 mm
Depth	44.6 mm
Min. material thickness	1 mm

Notes

General	A cover segment should be used if terminal blocks with a higher number of terminal points cannot be covered by the contour of another terminal block.
---------	---

DS-PTIO 1,5/S - Cover segment

1045987

<https://www.phoenixcontact.com/us/products/1045987>



Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DS-PTIO 1,5/S - Cover segment



1045987
<https://www.phoenixcontact.com/us/products/1045987>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com