

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Blind plug, nom. voltage: 250 V, nominal current: 24 A, Rated cross section: 6 mm², color: gray

Commercial data

Item number	1029338
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BE6114
Catalog page	Page 651 (C-1-2019)
GTIN	4055626531380
Weight per piece (including packing)	139.5 g
Weight per piece (excluding packing)	139.5 g
Customs tariff number	85389099
Country of origin	PL

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Technical data

Product properties

Product type	Blind plug
--------------	------------

Connection data

Nominal current	24 A
Maximum load current	24 A
Nominal voltage	250 V
Nominal cross section	6 mm ²

Material specifications

Color	gray
Flammability rating according to UL 94	V0
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Drawings

Circuit diagram



FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/pc/products/1029338>



CSA
Approval ID: 13631



cUL Recognized
Approval ID: FILE E 60425



UL Recognized
Approval ID: FILE E 60425

cULus Recognized

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Classifications

ECLASS

ECLASS-11.0	27440313
ECLASS-13.0	27440313
ECLASS-12.0	27440313

ETIM

ETIM 8.0	EC002255
----------	----------

UNSPSC

UNSPSC 21.0	20122000
-------------	----------

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Environmental product compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



Accessories

BTFE 6-3/14 AUX - Test terminal strip

1029253

<https://www.phoenixcontact.com/pc/products/1029253>



Test terminal strip, nom. voltage: 400 V, nominal current: 24 A, connection method: Ring cable lug, 1 level, mounting type: Wall mounting, color: gray

TMT (EX6,2)R - Marker for terminal blocks

0803063

<https://www.phoenixcontact.com/pc/products/0803063>



Marker for terminal blocks, Roll, white, unlabeled, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: snapped, snap into flat marker groove, lettering field size: 6.2 x 50000 mm, Number of individual labels: 1

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



ZBF 8:UNBEDRUCKT - Zack Marker strip, flat

0808781

<https://www.phoenixcontact.com/pc/products/0808781>



Zack Marker strip, flat, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

ZBF 8 CUS - Zack Marker strip, flat

0825030

<https://www.phoenixcontact.com/pc/products/0825030>



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



ZBF 8,LGS:FORTL.ZAHLEN - Zack Marker strip, flat

0808804

<https://www.phoenixcontact.com/pc/products/0808804>



Zack Marker strip, flat, Strip, white, labeled, printed horizontally: consecutive numbers 1 ... 10, 11 ... 20, etc. up to 101 ... 110, mounting type: snapped, for terminal block width: 8 mm, lettering field size: 5.15 x 8.15 mm, Number of individual labels: 10

UC-TMF 8 - Marker for terminal blocks

0818137

<https://www.phoenixcontact.com/pc/products/0818137>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.6 x 5.1 mm, Number of individual labels: 56

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



UC-TMF 8 CUS - Marker for terminal blocks

0824654

<https://www.phoenixcontact.com/pc/products/0824654>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8.2 mm, lettering field size: 7.6 x 5.1 mm, Number of individual labels: 56

UCT-TMF 8 - Marker for terminal blocks

0828748

<https://www.phoenixcontact.com/pc/products/0828748>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, for terminal block width: 8.2 mm, lettering field size: 7.4 x 4.7 mm, Number of individual labels: 42

FBP-3F/14 AUX - Blind plug

1029338

<https://www.phoenixcontact.com/pc/products/1029338>



UCT-TMF 8 CUS - Marker for terminal blocks

0829672

<https://www.phoenixcontact.com/pc/products/0829672>



Marker for terminal blocks, can be ordered: by sheet, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8.2 mm, lettering field size: 7.4 x 4.7 mm, Number of individual labels: 42

US-TMF 100 - Marker for terminal blocks

0829260

<https://www.phoenixcontact.com/pc/products/0829260>



Marker for terminal blocks, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped, snap into flat marker groove, lettering field size: 104 x 6.6 mm, Number of individual labels: 20

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com