REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图框升级整理图面	2024.07.27	阿 树









2P



3P



4P



5P



6P



■SPECIFICATIONS
- •Voltage rating:250V AC/DC
- •Current rating:7A AC/DC
- •Withstanding Voltage:1500V AC/minute
- •Temperature range:−45°C+125°C
- •Insulation resistance:≥1000MΩ
- •Contact resistance:≤20mΩ

PART NO.:

X9357 H M−02 N2 XX
① ② ③ ④ ⑤ ⑥

① Series No
② Category:H−HSG
③ Welding Board Angle:M−Male Housing
④ Row No−Pin No：XX−02P~06P
⑤ Material:N0−PA66 UL94V−0;N2−PA66 UL94V−2
⑥ Color：Blank−Natural Color

Poles	Dimensions(mm)	
	A	B
02	9.50	4.20
03	13.70	8.40
04	17.90	12.60
05	22.10	16.80
06	26.30	21.00

X9357HM−02−N0	Nylon 66 94V−2	X9357TM	X9357M Or X9357H
X9357HM−02−N2			
PART N0	Material	Suitable XKB Terminal	Suitable XKB Terminal

ANGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

DESIGN	阿 树	VIEW:	MODEL TYPE: 4.20 mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X9357HM−02−N2
APPROVED		SIZE: A4	DWG NO.: X−X9357HM−02−N2

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1