

# Data sheet

## 3700.2 ZAP 2,5/2A BG



End plate, Width: 2 mm, Colour: Beige

### Business data

|                                            |               |
|--------------------------------------------|---------------|
| Article number                             | <u>3700.2</u> |
| Article name                               | ZAP 2,5/2A BG |
| GTIN (EAN)                                 | 4044211060015 |
| Packaging unit                             | 50            |
| Quantity unit                              | PC            |
| Weight per piece (not including packaging) | 2.4 g         |
| Weight per piece (including packaging)     | 2.5 g         |
| Unit of weight                             | G             |
| Customs number                             | 85389099      |
| Country of origin                          | DE            |
| Prio-Article                               | 3700.2        |
| Product description                        | End plate     |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Length | 59 mm   |
| Width  | 2 mm    |
| Height | 30.8 mm |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Flammability class UL 94  | V-2           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 105 °C        |

#### Further technical data

|                       |   |
|-----------------------|---|
| Designed as end plate | ✓ |
| Snap-on available     | ✓ |

#### Environmental Product Compliance

|                                |     |
|--------------------------------|-----|
| REACH Conform                  | Yes |
| REACH Candidate Substance Note | No  |

---

Media

---

### Accessories

#### ##INVERSE##CONTA-CONNECT




Ex protective-earth terminal ATEX-certified Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name       | GTIN (EAN)    | Packaging unit |
|----------------|--------------------|---------------|----------------|
| <u>1713.2</u>  | ZSL 2,5/2A Ex GNYE | 4044211058548 | 100 ST         |



Protective earth terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Green-yellow

| Article number | Article name    | GTIN (EAN)    | Packaging unit |
|----------------|-----------------|---------------|----------------|
| <u>3510.2</u>  | ZSL 2,5/2A GNYE | 4044211151720 | 100 ST         |



Ex feed-through terminal ATEX-certified, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name     | GTIN (EAN)    | Packaging unit |
|----------------|------------------|---------------|----------------|
| <u>1704.2</u>  | ZRK 2,5/2A Ex BG | 4044211058401 | 100            |



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name       | GTIN (EAN)    | Packaging unit |
|----------------|--------------------|---------------|----------------|
| <u>1169.2</u>  | ZSRK 2,5/2A/SAS BG | 4044211128647 | 100            |



Feed-through terminal, Tension-spring connection, Mounting type: Mounting rail TS 35/7.5, Rated cross-section: 2.5 mm<sup>2</sup>, Width: 5.1 mm, Colour: Beige

| Article number | Article name  | GTIN (EAN)    | Packaging unit |
|----------------|---------------|---------------|----------------|
| <u>3500.2</u>  | ZRK 2,5/2A BG | 4044211151683 | 100            |