

# D-PTRV 4 WH D-A - End cover

3270237

<https://www.phoenixcontact.com/us/products/3270237>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, depth: 48.9 mm, width: 2.2 mm, height: 63.6 mm, color: white

## Your advantages

- Marked D ... A, can be read vertically
- Space-saving partition and end cover with isolating function
- Same shape as the PTRV... marshalling panel

## Commercial data

|                                      |                    |
|--------------------------------------|--------------------|
| Item number                          | 3270237            |
| Packing unit                         | 10 pc              |
| Sales key                            | BE69               |
| Product key                          | BE6Z1X             |
| Catalog page                         | Page 49 (C-1-2019) |
| GTIN                                 | 4055626260204      |
| Weight per piece (including packing) | 3.82 g             |
| Weight per piece (excluding packing) | 3.71 g             |
| Customs tariff number                | 85389099           |
| Country of origin                    | PL                 |

# D-PTRV 4 WH D-A - End cover



3270237

<https://www.phoenixcontact.com/us/products/3270237>

## Technical data

### Product properties

|              |           |
|--------------|-----------|
| Product type | End cover |
|--------------|-----------|

### Environmental and real-life conditions

#### Ambient conditions

|                                          |                                                                           |
|------------------------------------------|---------------------------------------------------------------------------|
| Ambient temperature (operation)          | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)       |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly)           | -5 °C ... 70 °C                                                           |
| Ambient temperature (actuation)          | -5 °C ... 70 °C                                                           |
| Permissible humidity (storage/transport) | 30 % ... 70 %                                                             |

### Material specifications

|                                        |       |
|----------------------------------------|-------|
| Color                                  | white |
| Material                               | PA    |
| Flammability rating according to UL 94 | V0    |

### Dimensions

|                 |         |
|-----------------|---------|
| Width           | 2.2 mm  |
| End cover width | 2.2 mm  |
| Height          | 63.6 mm |
| Depth           | 48.9 mm |

# D-PTRV 4 WH D-A - End cover



3270237

<https://www.phoenixcontact.com/us/products/3270237>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27141133 |
| ECLASS-12.0 | 27141133 |
| ECLASS-13.0 | 27250301 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000886 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# D-PTRV 4 WH D-A - End cover



3270237

<https://www.phoenixcontact.com/us/products/3270237>

## Environmental product compliance

|            |                                                         |
|------------|---------------------------------------------------------|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)