

CUC-PPC-C2ZNI-DC - Blind plug



1001432

<https://www.phoenixcontact.com/us/products/1001432>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Blind plug, degree of protection: IP65/IP67, material: Zinc die-cast, color: silver

Commercial data

Item number	1001432
Packing unit	1 pc
Sales key	AB17
Product key	ABNOHZ
Catalog page	Page 364 (C-2-2019)
GTIN	4055626469683
Weight per piece (including packing)	106.1 g
Weight per piece (excluding packing)	100.5 g
Customs tariff number	85366990
Country of origin	PL

Technical data

Notes

General	This product corresponds to the PROFINET Cabling and Interconnection Technology Guideline for PROFINET regulations, version 2.00, order no: 2.252, Chapter 11 Connectors for 24 Volt Power Supply Cabling and Chapter 13 Application specific Cabling and Interconnection Technology (AIDA)
---------	---

Product properties

Product type	Data plug
Application	Power

Dimensions

Width	31 mm
Height	36 mm
Length	67 mm

Material specifications

Color	silver
Material	Metal
Flammability rating according to UL 94	V0
Seal material	NBR
Housing surface material	nickel-plated
O-ring material	NBR
Housing material	Zinc die-cast

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65/IP67
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-10 °C ... 40 °C

CUC-PPC-C2ZNI-DC - Blind plug



1001432

<https://www.phoenixcontact.com/us/products/1001432>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440114

ETIM

ETIM 8.0	EC002635
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-PPC-C2ZNI-DC - Blind plug



1001432
<https://www.phoenixcontact.com/us/products/1001432>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com