

NBC-PP-F1PWH:10 - Plug Guard Security Frame



1041881

<https://www.phoenixcontact.com/us/products/1041881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plug Guard Security Frame



Product description

Plug Guard Security Frame, for securing the RJ45 interface against unauthorized disconnection, with key element

Your advantages

- Perfect for industrial applications
- Compact angle
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)

Commercial data

Item number	1041881
Packing unit	10 pc
Sales key	AB18
Product key	ABNLAZ
Catalog page	Page 375 (C-2-2019)
GTIN	4055626598567
Weight per piece (including packing)	2.18 g
Weight per piece (excluding packing)	2.18 g
Customs tariff number	85389099
Country of origin	CH

NBC-PP-F1PWH:10 - Plug Guard Security Frame



1041881

<https://www.phoenixcontact.com/us/products/1041881>

Technical data

Notes

General	For integration into DIN rail adapter NBC-PP-G1PGY
---------	--

Product properties

Product type	Female insert
Number of slots	1

Material specifications

Material	PC
Contact material	Copper alloy
Contact carrier material	LCP

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	PCB mounting
---------------	--------------

NBC-PP-F1PWH:10 - Plug Guard Security Frame




1041881

<https://www.phoenixcontact.com/us/products/1041881>

Drawings

Dimensional drawing



NBC-PP-F1PWH:10 - Plug Guard Security Frame



1041881

<https://www.phoenixcontact.com/us/products/1041881>

Classifications

ECLASS

ECLASS-11.0	27060308
ECLASS-12.0	27060308
ECLASS-13.0	27440292

ETIM

ETIM 9.0	EC002599
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

NBC-PP-F1PWH:10 - Plug Guard Security Frame



1041881

<https://www.phoenixcontact.com/us/products/1041881>

Mandatory accessories

NBC-PP-G1PGY - DIN rail adapter

1041740

<https://www.phoenixcontact.com/us/products/1041740>



DIN rail adapter, design: Headers with shielding, degree of protection: IP20, material: PC-GF10, connection method: Quick connection, without assembled modules

Accessories

NBC-PP-G1PGY - DIN rail adapter

1041740

<https://www.phoenixcontact.com/us/products/1041740>



DIN rail adapter, design: Headers with shielding, degree of protection: IP20, material: PC-GF10, connection method: Quick connection, without assembled modules

NBC-PP-F1PWH:10 - Plug Guard Security Frame




1041881

<https://www.phoenixcontact.com/us/products/1041881>

NBC-R4AC1/1,0-94G/R4AC1-BU - Patch cable

1413160

<https://www.phoenixcontact.com/us/products/1413160>



Patch cable, degree of protection: IP20, cable length: 1 m, number of positions: 8, 10 Gbps, CAT6_A, Ethernet

FL CAT5 PATCH 1,0 - Patch cable

2832276

<https://www.phoenixcontact.com/us/products/2832276>



Patch cable, CAT5, assembled, 1 m

NBC-PP-F1PWH:10 - Plug Guard Security Frame

1041881

<https://www.phoenixcontact.com/us/products/1041881>




FL CAT6 PATCH 1,0 - Patch cable

2891385

<https://www.phoenixcontact.com/us/products/2891385>

Patch cable, CAT6, preassembled, 1.0 m



Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com