

# DS-PT 2,5-MT - Cover segment

1043963

<https://www.phoenixcontact.com/us/products/1043963>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover segments, large segment: 29 x 12.1 x 2, small segment: 22.65 x 12.9 x 2, color: gray

## Commercial data

Item number	1043963
Packing unit	10 pc
Sales key	BE22
Product key	BE224Z
GTIN	4055626611785
Weight per piece (including packing)	0.772 g
Weight per piece (excluding packing)	0.531 g
Customs tariff number	85389099
Country of origin	PL

# DS-PT 2,5-MT - Cover segment

1043963

<https://www.phoenixcontact.com/us/products/1043963>



## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0

### Dimensions

Width	2 mm
End cover width	2 mm
Height	56.7 mm
Depth	12.9 mm

### Notes

General	A cover segment should be used if terminal blocks with a higher number of terminal points cannot be covered by the contour of another terminal block.
---------	---

# DS-PT 2,5-MT - Cover segment



1043963

<https://www.phoenixcontact.com/us/products/1043963>

## Classifications

### ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

### ETIM

ETIM 9.0	EC000886
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# DS-PT 2,5-MT - Cover segment



1043963

<https://www.phoenixcontact.com/us/products/1043963>

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)