

D-PTRV 8 WH 8-1 - End cover

3270242

<https://www.phoenixcontact.com/us/products/3270242>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



End cover, depth: 80.8 mm, width: 2.2 mm, height: 100 mm, color: white

Your advantages

- Marked 8 ... 1, can be read vertically
- Space-saving partition and end cover with isolating function
- Same shape as the PTRV... marshalling panel

Commercial data

Item number	3270242
Packing unit	10 pc
Sales key	BE69
Product key	BE6Z1X
Catalog page	Page 53 (C-1-2019)
GTIN	4055626260259
Weight per piece (including packing)	8.03 g
Weight per piece (excluding packing)	8.03 g
Customs tariff number	85389099
Country of origin	PL

D-PTRV 8 WH 8-1 - End cover



3270242

<https://www.phoenixcontact.com/us/products/3270242>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	white
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	2.2 mm
End cover width	2.2 mm
Height	100 mm
Depth	80.8 mm

D-PTRV 8 WH 8-1 - End cover



3270242

<https://www.phoenixcontact.com/us/products/3270242>

Classifications

ECLASS

ECLASS-11.0	27141133
ECLASS-12.0	27141133
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

D-PTRV 8 WH 8-1 - End cover



3270242

<https://www.phoenixcontact.com/us/products/3270242>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com