REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		独立各PIN数图纸，增加开孔定位尺寸	2024.12.7	阿树







Specifications:
规格：
1.Voltage rating:250VAC/DC
额定电压：250V AC/DC
2.Current rating:3A AC/DC
额定电流：3A AC/DC
3.Withstanding voltage:500V AC/minute
耐受电压：500V AC/分钟
4.Temperature range: −55℃−+105℃
温度范围：−55℃−+105℃
5.Insulation resistance:1000MΩ MIN
绝缘电阻：1000MΩ MIN
6.Contact resistance:30mΩ Max
接触电阻：30mΩ Max
Materiai:
材料：
7.Rubber core:PBT UL94V−0
胶芯：PBT UL94V−0
8.The iron shell:SPCC−SD Nivkel Plating; Tin Plating/Gold Plating
铁壳：SPCC−SD,镀镍/镀锡/镀金
9.Terminal:Copper alloy
端子：铜合金

铆合方式	TYPE-1:铆合	TYPE-2:前铆实心螺母	TYPE-3:后铆空心螺母	TYPE-4:后铆空心螺母锁螺丝
图示				

PART NO.:

X04 62 F C 2 B 1
① ② ③ ④ ⑤ ⑥ ⑦

①Series No
②Pin No.:62PIN
③Welding Board Angle :F−Female
④T:Tradutional C：Car−pin
⑤Planting Categotry:
1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
⑥Color:B−BLACK W−White BL−Blue
⑦1:TYPE−1; 2:TYPE−2; 3:TYPE−3; 4:TYPE−4

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	

XKB 星创 Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿树	VIEW:	MODEL TYPE: D−SUB
CHECKED		UNIT: mm/in	PART NO.: X0462FC2B1
APPROVED		SIZE: A4	DWG NO.: X-X0462FC2B1
			SCALE N/A / PAGE 1/1 / REVISION A1

www.helloxkb.com www.helloxkb.cn www.xk−dg.cn